



640 Series Copper Cable, category 6A, 4 pair, UTP, LSZH, 23 AWG, 1000 ft reel, white

### **OBSOLETE**

**This product was discontinued on: November 1, 2017**

#### **Replaced By**

884036104/10 CS44Z3 WHT C6A 4/23 U/UTP RL 305M	CS44Z3 ETL Verified Category 6A U/UTP LSZH Cable, white jacket, 4 pair count, 1000 ft (305 m) length, reel
884036114/10 CS44Z3 WHT C6A 4/23 U/UTP CPK 305M	CS44Z3 ETL Verified Category 6A U/UTP LSZH Cable, white jacket, 4 pair count, 1000 ft (305 m) length, CommPak
884036134/32 CS44Z3 WHT C6A 4/23 U/UTP RL 1KM	CS44Z3 ETL Verified Category 6A U/UTP LSZH Cable, white jacket, 4 pair count, 3280 ft (1000 m) length, reel

## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Series</b>	640 Series
<b>Product Type</b>	Twisted pair cable
<b>Regional Availability</b>	Australia/New Zealand

## Standards And Qualifications

**EN50575 CPR Cable EuroClass** Dca | s2 | d2

## Construction Materials

<b>Jacket Material</b>	Low Smoke Zero Halogen (LSZH)
<b>Conductor Material</b>	Bare copper

## Dimensions

**Cable Length** 305 m | 1000 ft

## Electrical Specifications

<b>ANSI/TIA Category</b>	6A
<b>Operating Voltage, maximum</b>	80 V
<b>Transmission Standards</b>	ANSI/TIA-568-C.2   CENELEC EN 50288-6-1   ISO/IEC 11801 Class E

## Environmental Specifications

**Operating Temperature** -20 °C to +60 °C (-4 °F to +140 °F)

## General Specifications

**Cable Type** U/UTP (unshielded)  
**Packaging Type** Reel  
**Pairs, quantity** 4  
**Cable Component Type** Horizontal  
**Jacket Color** White  
**Product Number** 640Z  
**Conductor Type, singles** Solid

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available

