



High Density M-Series Adapter, white

Product Classification

Portfolio	CommScope®
Product Type	Adapter
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Depth	9.14 mm 0.36 in
Height	17.53 mm 0.69 in
Width	18.54 mm 0.73 in

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Color	White
Ordering Note	Minimum order quantity, 20 packs
Package Quantity	25

Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

