


## High Density M-Series Adapter, ivory



### Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Adapter
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

### Dimensions

<b>Depth</b>	9.14 mm   0.36 in
<b>Height</b>	17.53 mm   0.69 in
<b>Width</b>	18.54 mm   0.73 in

### Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Safety Standard</b>	cUL   UL
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

### General Specifications

<b>Color</b>	Ivory
<b>Ordering Note</b>	Minimum order quantity, 20 packs
<b>Package Quantity</b>	25

### Mechanical Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic
----------------------	---

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

