

SVAPA15V300



HomeConnect® Power Adapter for Subscriber Amplifiers, ac/dc, 15 V, 300 mA

Product Classification

Brand	HomeConnect®
Product Type	RF amplifier power adapter

Environmental Specifications

Safety Standard	c-UL-us
------------------------	---------

Electrical Specifications

Plug Type	Type A
Input Current, maximum	60 mA
Input Voltage	120 Vac @ 60 Hz
Operating Current at Voltage	300 mA @ 15 Vdc
Output Voltage Tolerance, no load	±5%
Output Voltage, no load	20.3 Vdc

Packed Dimensions

Carton Quantity	80
Height	330.20 mm 13.00 in
Length	381.00 mm 15.00 in
Width	304.80 mm 12.00 in
Shipping Weight	19.05 kg 42.00 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

