

SVAPA15V300C

HomeConnect® Power Adapter for Subscriber Amplifiers, ac/dc, 15 V, 300 mA



Product Classification

Brand HomeConnect®
Product Type RF amplifier power adapter

Environmental Specifications

Safety Standard CE

Electrical Specifications

Plug Type Type C
Input Current, maximum 35 mA
Input Voltage 230 Vac @ 50 Hz
Operating Current at Voltage 300 mA @ 15 Vdc
Output Voltage Tolerance, no load ±5%
Output Voltage, no load 20.7 Vdc

Packed Dimensions

Carton Quantity 100
Height 279.40 mm | 11.00 in
Length 381.00 mm | 15.00 in
Width 304.80 mm | 12.00 in
Shipping Weight 19.96 kg | 44.00 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

