



HomeConnect® F81 Barrel Splice, all-thread

Product Classification

Brand	HomeConnect®
Product Type	Barrel splice

Environmental Specifications

Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Safety Standard	CE EN 60728-4 SCTE

Electrical Specifications

Impedance	75 ohm
Operating Frequency Band	0 – 3000 MHz
Insertion Loss at Frequency Band, maximum	0.2 dB @ 0–1002 MHz 0.3 dB @ 1002–3000 MHz
Return Loss at Frequency Band, minimum	20 dB @ 2000–3000 MHz 25 dB @ 1002–2000 MHz 35 dB @ 0–1002 MHz
Shielding Effectiveness, minimum	120 dB

General Specifications

Device Type	F81 barrel splice
--------------------	-------------------

Dimensions

Length	26.42 mm 1.04 in
---------------	--------------------

Mechanical Specifications

Material Type	Brass
Plating	Nickel

Packed Dimensions

Carton Quantity	3000
Height	190.50 mm 7.50 in

SVF81GAC

Length	330.20 mm 13.00 in
Width	241.30 mm 9.50 in
Shipping Weight	19.96 kg 44.00 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

