



1-5/8 EIA Coupling Element, O-Ring, screw-set

## Product Classification

**Product Type** Coupling element

## General Specifications

**Interface** 1-5/8 in EIA Flange  
**Includes** O-rings | Screw set

## Electrical Specifications

**Connector Impedance** 50 ohm  
**Operating Frequency Band** 0 – 5200 MHz

## Mechanical Specifications

**Inner Contact Plating** Silver

## Dimensions

**Height** 41.50 mm | 1.63 in  
**Length** 68.20 mm | 2.69 in  
**Weight** 0.20 kg | 0.44 lb  
**Width** 41.50 mm | 1.63 in

## Standard Conditions

**Attenuation, Ambient Temperature** 20 °C | 68 °F  
**Average Power, Ambient Temperature** 20 °C | 68 °F  
**Average Power, Inner Conductor Temperature** 100 °C | 212 °F

## Regulatory Compliance/Certifications

| Agency                           | Classification   |
|----------------------------------|--|
| RoHS 2011/65/EU<br>ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

