



3-1/8 EIA Coupling Element, O-Ring, screw-set

Product Classification

Product Type Coupling element

General Specifications

Interface 3-1/8 in EIA Flange
Includes O-rings | Screw set

Electrical Specifications

Connector Impedance 50 ohm
Operating Frequency Band 1 – 5200 MHz

Mechanical Specifications

Inner Contact Plating Silver

Dimensions

Height 81.30 mm | 3.20 in
Length 101.10 mm | 3.98 in
Weight 0.50 kg | 1.10 lb
Width 81.30 mm | 3.20 in

Standard Conditions

Attenuation, Ambient Temperature 20 °C | 68 °F
Average Power, Ambient Temperature 20 °C | 68 °F
Average Power, Inner Conductor Temperature 100 °C | 212 °F

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

