



4-1/2 IEC Coupling Element, O-Ring, screw-set

Product Classification

Product Type Coupling element

General Specifications

Interface 4-1/2 in EIA/IEC Flange
Includes O-rings | Screw set

Electrical Specifications

Connector Impedance 50 ohm
Operating Frequency Band 1 – 5200 MHz

Mechanical Specifications

Inner Contact Plating Silver

Dimensions

Height 104.75 mm | 4.12 in
Length 76.60 mm | 3.02 in
Weight 0.61 kg | 1.34 lb
Width 104.75 mm | 4.12 in

Standard Conditions

Attenuation, Ambient Temperature 20 °C | 68 °F
Average Power, Ambient Temperature 20 °C | 68 °F
Average Power, Inner Conductor Temperature 100 °C | 212 °F

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

