

# CSAPAE415V500

Power Adapter for Subscriber Amplifiers, ac/dc, 15 V, 500 mA



## Product Classification

**Brand** HomeConnect®  
**Product Type** RF amplifier power adapter

## Environmental Specifications

**Energy Efficiency Standard** EISA 2007, Level 4  
**Safety Standard** c-UL-us

## Electrical Specifications

**Plug Type** Type A  
**Input Current, maximum** 250 mA  
**Input Voltage** 120 Vac @ 60 Hz  
**Operating Current at Voltage** 500 mA @ 15 Vdc  
**Output Voltage Tolerance, no load** ±5%  
**Output Voltage, no load** 24.0 Vdc

## Packed Dimensions

**Carton Quantity** 60  
**Height** 254.00 mm | 10.00 in  
**Length** 469.90 mm | 18.50 in  
**Width** 469.90 mm | 18.50 in  
**Shipping Weight** 22.00 kg | 48.50 lb

## Regulatory Compliance/Certifications

**Agency** ISO 9001:2015  
**Classification** Designed, manufactured and/or distributed under this quality management system

