

# CSAPAE615V500



Power Adapter for Subscriber Amplifiers, ac/dc, 15 V, 500 mA, EISA VI

## Product Classification

<b>Brand</b>	HomeConnect®
<b>Product Type</b>	RF amplifier power adapter

## Environmental Specifications

<b>Energy Efficiency Standard</b>	EISA 2016, Level 6
<b>Safety Standard</b>	c-UL-us

## Electrical Specifications

<b>Plug Type</b>	Type A
<b>Input Current, maximum</b>	190 mA
<b>Input Voltage, specific</b>	100-240 Vac @ 50-60 Hz
<b>Inrush Current, maximum</b>	30.00 A
<b>Operating Current at Voltage</b>	500 mA @ 15 Vdc
<b>Output Load Regulation Tolerance, maximum</b>	±5%
<b>Output Power, maximum</b>	7.5 W
<b>Output Voltage Ripple, maximum</b>	150 mVpp

## Packed Dimensions

<b>Carton Quantity</b>	100
<b>Height</b>	408.94 mm   16.10 in
<b>Length</b>	594.36 mm   23.40 in
<b>Width</b>	381.00 mm   15.00 in
<b>Shipping Weight</b>	22.00 kg   48.50 lb

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

