

BNC-26B-N

Straight BNC Connector RF, image360, SDV-25

Product Classification

Product Type	Broadcast video connector
Regional Availability	North America

General Specifications

Body Style	Straight
Compatible Cable type	SDV-25
Interface	BNC Male
Package Quantity	100

Electrical Specifications

Connector Impedance	75 ohm
Insulation Resistance, minimum	200 MOhm
Voltage Rating	1000 V

Mechanical Specifications

Attachment Durability	500 cycles
Inner Contact Attachment Method	Crimp
Outer Contact Attachment Method	Crimp

Environmental Specifications

Flammability	UL 94-V0
Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	0%–95%, non-condensing
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

