

ATCP-D38



ProAx® American Triax Complete Camera Connector Male Plug, D38 (3/8\"), 0.410\" cables, 75 ohms

Product Classification

Brand	ProAx®
Product Series	ProAx
Product Type	Broadcast camera connector
Regional Availability	North America

General Specifications

Body Style	Straight
Compatible Cable type	D38 (0.410\")
Interface	Triax plug, male
Material Type	Brass
Package Quantity	1
Plating Type	Nickel

Electrical Specifications

Connector Impedance	75 ohm
Voltage Rating	1000 Vac

Mechanical Specifications

Attachment Durability	1000 cycles
Inner Contact Attachment Method	Crimp
Outer Contact Attachment Method	Crimp

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	0%–95%, non-condensing
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)

ATCP-D38

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

