

## LightCrimp Plus™ Fiber Optic Connector Kit,, 62.5/125 μm

### Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Brand</b>	LightCrimp Plus™
<b>Product Series</b>	SECURE
<b>Product Type</b>	Fiber connector
<b>Regional Availability</b>	Asia   Latin America   North America

### Construction Materials

<b>Fiber Type</b>	OM1
<b>Ferrule Geometry</b>	Factory polished
<b>Fiber Mode</b>	Multimode

### Dimensions

**Compatible Cable Diameter** 0.9 mm | 0.0 in

### General Specifications

<b>Interface</b>	LC
<b>Body Style</b>	Simplex
<b>Interface Feature</b>	Standard   Epoxyless
<b>Color</b>	Green
<b>Application</b>	For use with buffered fiber
<b>Boot Style</b>	Short
<b>Color, boot</b>	Beige
<b>Package Quantity</b>	1
<b>Packaging Type</b>	Bag

### Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

