



## AMP STACK™ III Connector Splice Kit, pre-sealed, 25-pair

### Product Classification

|                              |                                                                     |
|------------------------------|---------------------------------------------------------------------|
| <b>Brand</b>                 | AMP STACK™                                                          |
| <b>Product Type</b>          | Connector kit                                                       |
| <b>Product Series</b>        | AMP STACK                                                           |
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |

### Dimensions

**Compatible Insulated Conductor Diameter, maximum** 1.650 mm | 0.065 in

### Environmental Specifications

**Environmental Space** Outdoor

### General Specifications

|                                |                                   |
|--------------------------------|-----------------------------------|
| <b>Color</b>                   | Gold ivory   Transparent          |
| <b>Connector Sealant</b>       | Gel filled                        |
| <b>Connector Splicing Type</b> | Straight (In-line)                |
| <b>Includes</b>                | Base with covers                  |
| <b>Ordering Note</b>           | Minimum order quantity, 120 parts |
| <b>Package Quantity</b>        | 12                                |
| <b>Packaging Type</b>          | Bag   Box                         |
| <b>Pairs, quantity</b>         | 25                                |

### Mechanical Specifications

|                                 |                            |
|---------------------------------|----------------------------|
| <b>Conductor Gauge, solid</b>   | 28–20 AWG                  |
| <b>Contact Base Material</b>    | Phosphor bronze            |
| <b>Contact Plating Material</b> | Tin                        |
| <b>Material Type</b>            | Glass filled polycarbonate |

### Regulatory Compliance/Certifications

|                 |                       |
|-----------------|-----------------------|
| <b>Agency</b>   | <b>Classification</b> |
| RoHS 2011/65/EU | Compliant             |

