

BNC-10B-N

Straight BNC Connector RF, RG 1695A, RG6SD-PLEN

Product Classification

Product Type Broadcast video connector
Regional Availability North America

General Specifications

Body Style Straight
Compatible Cable type RG 1694A | RG 6SD-PLEN
Interface BNC Male
Package Quantity 100

Electrical Specifications

Connector Impedance 75 ohm
Insulation Resistance, minimum 200 MOhm
Voltage Rating 1000 V

Mechanical Specifications

Attachment Durability 500 cycles
Inner Contact Attachment Method Crimp
Outer Contact Attachment Method Crimp

Environmental Specifications

Flammability UL 94-V0
Operating Temperature -40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity 0%–95%, non-condensing
Storage Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

