



AMP STACK™ IV Connector Splice Kit, dry, 10-pair

## Product Classification

<b>Brand</b>	AMP STACK™
<b>Product Type</b>	Connector kit
<b>Product Series</b>	AMP STACK
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

**Compatible Insulated Conductor Diameter, maximum** 1.960 mm | 0.077 in

## Environmental Specifications

**Environmental Space** Outdoor

## General Specifications

<b>Color</b>	Gold ivory   Transparent
<b>Connector Sealant</b>	Dry
<b>Connector Splicing Type</b>	Straight (In-line)
<b>Includes</b>	Base with covers
<b>Ordering Note</b>	Minimum order quantity, 120 parts
<b>Package Quantity</b>	12
<b>Packaging Type</b>	Bag   Box
<b>Pairs, quantity</b>	10

## Mechanical Specifications

<b>Conductor Gauge, solid</b>	26–19 AWG
<b>Contact Base Material</b>	Phosphor bronze
<b>Contact Plating Material</b>	Tin
<b>Material Type</b>	Glass filled polycarbonate

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant

