

BNC-8-N

Straight BNC Coax Connectors, 1694A

Product Classification

Product Type Broadcast video connector
Regional Availability North America

General Specifications

Body Style Straight
Compatible Cable type RG 1694A
Interface BNC Male
Package Quantity 1

Electrical Specifications

Connector Impedance 75 ohm
Insulation Resistance, minimum 200 MOhm
Voltage Rating 1000 V

Mechanical Specifications

Attachment Durability 500 cycles
Inner Contact Attachment Method Crimp
Outer Contact Attachment Method Crimp

Environmental Specifications

Flammability UL 94-V0
Operating Temperature -40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity 0%–95%, non-condensing
Storage Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

