

# BNC-1-N

## Straight BNC Coax Connectors, 734, 1505A



### Product Classification

<b>Product Type</b>	Broadcast video connector
<b>Regional Availability</b>	North America

### General Specifications

<b>Body Style</b>	Straight
<b>Compatible Cable type</b>	RG 1505A   RG 734
<b>Interface</b>	BNC Male
<b>Package Quantity</b>	1

### Electrical Specifications

<b>Connector Impedance</b>	75 ohm
<b>Insulation Resistance, minimum</b>	200 MOhm
<b>Voltage Rating</b>	1000 V

### Mechanical Specifications

<b>Attachment Durability</b>	500 cycles
<b>Inner Contact Attachment Method</b>	Crimp
<b>Outer Contact Attachment Method</b>	Crimp

### Environmental Specifications

<b>Flammability</b>	UL 94-V0
<b>Operating Temperature</b>	-40 °C to +65 °C (-40 °F to +149 °F)
<b>Relative Humidity</b>	0%–95%, non-condensing
<b>Storage Temperature</b>	-55 °C to +85 °C (-67 °F to +185 °F)

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant

