

BNC-10-N

Straight BNC Coax Connectors, 1695A, CD7506, VSD2001TS, single

Product Classification

Product Type Broadcast video connector
Regional Availability North America

General Specifications

Body Style Straight
Compatible Cable type CD7506 | RG 1695A | VSD2001TS
Interface BNC Male
Package Quantity 1

Electrical Specifications

Connector Impedance 75 ohm
Insulation Resistance, minimum 200 MOhm
Voltage Rating 1000 V

Mechanical Specifications

Attachment Durability 500 cycles
Inner Contact Attachment Method Crimp
Outer Contact Attachment Method Crimp

Environmental Specifications

Flammability UL 94-V0
Operating Temperature -40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity 0%–95%, non-condensing
Storage Temperature -55 °C to +85 °C (-67 °F to +185 °F)

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

