

ATCJ-C12



ProAx® American Triax Complete Camera Connector Female Jack, C12 (1/2"), 0.520" cables, 75 ohms

Product Classification

| | |
|------------------------------|----------------------------|
| Brand | ProAx® |
| Product Series | ProAx |
| Product Type | Broadcast camera connector |
| Regional Availability | North America |

General Specifications

| | |
|------------------------------|--------------------|
| Body Style | Straight |
| Compatible Cable type | C12 (0.520") |
| Interface | Triax jack, female |
| Material Type | Brass |
| Package Quantity | 1 |
| Plating Type | Nickel |

Electrical Specifications

| | |
|----------------------------|----------|
| Connector Impedance | 75 ohm |
| Voltage Rating | 1000 Vac |

Mechanical Specifications

| | |
|--|-------------|
| Attachment Durability | 1000 cycles |
| Inner Contact Attachment Method | Crimp |
| Outer Contact Attachment Method | Crimp |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Operating Temperature | -40 °C to +65 °C (-40 °F to +149 °F) |
| Relative Humidity | 0%–95%, non-condensing |
| Storage Temperature | -55 °C to +85 °C (-67 °F to +185 °F) |

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

