



AMP-TWIST SL-Series Modular Jack, 8-position, category 7AS, shielded, without dust cover

Product Classification

Portfolio	NETCONNECT®
Product Series	SL Series
Product Type	Modular jack
Regional Availability	Australia/New Zealand EMEA Latin America

Dimensions

Compatible Cable Diameter, maximum	9.00 mm 0.35 in
Compatible Insulated Conductor Diameter, maximum	1.600 mm 0.063 in
Depth	34.00 mm 1.34 in
Height	26.21 mm 1.03 in
Width	14.48 mm 0.57 in

Electrical Specifications

Transmission Standard	ANSI/TIA-568-C.2 ISO/IEC 11801 Class FA
------------------------------	---

Environmental Specifications

Flammability Rating	UL 94 V-0
----------------------------	-----------

General Specifications

Cable Type	Shielded
Color	Silver
Package Quantity	10
Packaging Type	Tray in box
Panel Cutout, recommended	14.78 x 20.32 mm (0.58 x 0.80 in)
Panel Thickness, recommended	1.60 mm

Mechanical Specifications

Conductor Gauge, solid	24–22 AWG
Conductor Gauge, stranded	26–24 AWG

Conductor Type	Solid Stranded
Contact Base Material	Beryllium copper
Contact Plating Material	Gold
Contact Plating Thickness	1.27 μ m
Material Type	Zinc alloy
Outlet Type	Standard
Termination Tool	SL Termination tool
Termination Type	IDC
Wiring	T568A T568B

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

