

## LightCrimp Plus™ Fiber Optic Kit, LC, simplex, 50/125 μm, jacketed



## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Brand</b>	LightCrimp Plus™
<b>Product Series</b>	LightCrimp
<b>Product Type</b>	Fiber connector
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   North America

## Construction Materials

<b>Fiber Type</b>	OM2
<b>Ferrule Geometry</b>	Factory polished
<b>Fiber Mode</b>	Multimode

## Dimensions

<b>Compatible Cable Diameter, maximum</b>	2.00 mm   0.08 in
<b>Compatible Cable Diameter, minimum</b>	1.60 mm   0.06 in

## General Specifications

<b>Interface</b>	LC
<b>Body Style</b>	Simplex
<b>Interface Feature</b>	Epoxyless   Standard
<b>Color</b>	Beige
<b>Application</b>	For use with jacketed fiber cable
<b>Color, boot</b>	Black
<b>Package Quantity</b>	1
<b>Packaging Type</b>	Bag

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

