



Modular Plug Kit, category 5e, shielded, 8-position, 5.1 – 6.0 mm max cable jack OD, 500/bag

Product Classification

Portfolio	CommScope®
Product Type	Modular plug
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Compatible Cable Diameter, maximum	6.00 mm 0.24 in
Compatible Cable Diameter, minimum	5.10 mm 0.20 in
Compatible Insulated Conductor Diameter, maximum	1.090 mm 0.043 in
Compatible Insulated Conductor Diameter, minimum	0.890 mm 0.035 in

Electrical Specifications

ANSI/TIA Category	5e
Insulation Resistance, minimum	500 mOhm

Environmental Specifications

Operating Temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Safety Standard	UL 1863

General Specifications

Cable Type	Round, shielded
Interface	RJ45
Package Quantity	500
Packaging Type	Bag Box Carton
Positions/Loaded Contacts	8/8

Mechanical Specifications

Conductor Gauge, solid	26–23 AWG
Conductor Gauge, stranded	26–23 AWG
Conductor Type	Solid Stranded
Contact Base Material	Phosphor bronze
Contact Plating Material	Gold

Contact Plating Thickness	1.27 μ m
Material Type	Glass filled polycarbonate
Plug Insertion Life, minimum	750 times
Plug Shield Base Material	Stainless steel
Plug Shield Plating Material	Nickel
Termination Type	IDC

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

