



PICABOND® Connector, 250 loose piece, green

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for butt, straight, bridge and half-tap splicing applications

Product Classification

Brand	PICABOND®
Product Type	Splice
Product Series	PICABOND
Regional Availability	Australia/New Zealand EMEA Latin America North America

Electrical Specifications

Safety Voltage Rating 400 Vdc

Environmental Specifications

Environmental Space Outdoor

Operating Temperature -40 °C to +60 °C (-40 °F to +140 °F)

General Specifications

Connector Color Code Green

Connector Sealant Unfilled

Connector Splicing Type Bridge | Butt | Full bridge | Half-tap | Straight (In-line)

Insulation Material Air Core PIC | Paper or Pulp

Package Quantity 250

Packaging Type Loose piece

Mechanical Specifications

Conductor Gauge, solid 26–22 AWG

Contact Base Material Phosphor bronze

Contact Plating Material Tin

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

