



PICABOND® Connector, 1000 loose piece, green/amber, breakaway, unfilled

- Lightweight, compact, and economical means of splicing multiconductor telephone cable
- No prestripping or cutting required, can tap without service interruptions, eliminates “turndowns”
- Color-coded to indicate size and type of wire; used for standard load coil, breakaway load coil and breakaway (add slack) splicing applications

Product Classification

Brand	PICABOND®
Product Type	Splice
Product Series	PICABOND
Regional Availability	Australia/New Zealand EMEA Latin America North America

Electrical Specifications

Safety Voltage Rating 400 Vdc

Environmental Specifications

Environmental Space Outdoor
Operating Temperature -40 °C to +60 °C (-40 °F to +140 °F)

General Specifications

Connector Color Code	Green/Amber
Connector Sealant	Unfilled
Connector Splicing Type	Breakaway (add slack) Breakaway Load Coil Standard Load Coil
Insulation Material	Air Core PIC Paper or Pulp
Package Quantity	1000
Packaging Type	Loose piece

Mechanical Specifications

Conductor Gauge, solid 26–22 AWG
Contact Base Material Phosphor bronze
Contact Plating Material Tin

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

