



RJ45 Patch Cord, category 6, UTP, solid, blue, 40 m

Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA

Dimensions

Cord Length	40.00 m 131.23 ft
Diameter Over Jacket	6.20 mm 0.24 in

Electrical Specifications

ANSI/TIA Category	6
--------------------------	---

Environmental Specifications

Environmental Space	Riser
Flammability Rating	CM

General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Blue
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Solid
Conductor Gauge, solid	23 AWG
Conductor Material	Bare copper

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

