

Fiber Optic Simplex Adapter, Multimode E2000/UPC, beige, with FIST retainer

- High quality zirconia ceramic split sleeves ensuring high precision alignment, reliability and improved reconnect ability
- Translucent easy grip dust cap and integrated mounting clips
- High quality one piece housing, no ultrasonic welding

Product Classification

Product Series	OC-ADK
Product Type	Fiber adapter
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Alignment Sleeve Material	Ceramic
Fiber Mode	Multimode

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

General Specifications

Interface	E2000
Body Style	Simplex
Interface Feature	Standard
Color	Beige
Package Quantity	1
Packaging Type	Bag
Total Ports, quantity	1
Transmission Standards	IEC 60754-1 IEC 61300-3-42

Mechanical Specifications

Coupling Retention Force	70.00 N 15.74 lbf
Mount Type	Square flange

Optical Performance

Insertion Loss, maximum	0.10 dB
--------------------------------	---------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

