



AMP STACK™ III Connector Splice Kit, pre-sealed, 25-pair

Product Classification

Brand	AMP STACK™
Product Type	Connector kit
Product Series	AMP STACK
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Compatible Insulated Conductor Diameter, maximum 1.650 mm | 0.065 in

Environmental Specifications

Environmental Space Outdoor

General Specifications

Color	Green ivory Transparent
Connector Sealant	Gel filled
Connector Splicing Type	Straight (In-line)
Includes	Base with covers
Ordering Note	Minimum order quantity, 120 parts
Package Quantity	12
Packaging Type	Bag Box
Pairs, quantity	25

Mechanical Specifications

Conductor Gauge, solid	28–20 AWG
Contact Base Material	Phosphor bronze
Contact Plating Material	Tin
Material Type	Glass filled polycarbonate

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

