

## Fiber Optic Simplex Connector Kit, Singlemode, rose



## Product Classification

|                              |                              |
|------------------------------|------------------------------|
| <b>Portfolio</b>             | NETCONNECT®                  |
| <b>Product Series</b>        | SECURE                       |
| <b>Product Type</b>          | Fiber connector              |
| <b>Regional Availability</b> | Australia/New Zealand   EMEA |

## Construction Materials

|                   |            |
|-------------------|------------|
| <b>Fiber Type</b> | OS2        |
| <b>Fiber Mode</b> | Singlemode |

## Dimensions

|   |                   |
|---|-------------------|
| <b>Compatible Cable Diameter, maximum</b> | 2.00 mm   0.08 in |
| <b>Compatible Cable Diameter, minimum</b> | 1.60 mm   0.06 in |

## General Specifications

|                          |                                   |
|--------------------------|-----------------------------------|
| <b>Interface</b>         | LC                                |
| <b>Body Style</b>        | Simplex                           |
| <b>Interface Feature</b> | Standard                          |
| <b>Color</b>             | Rose                              |
| <b>Application</b>       | For use with jacketed fiber cable |
| <b>Boot Style</b>        | Bend limiting                     |
| <b>Color, boot</b>       | Blue                              |
| <b>Package Quantity</b>  | 10                                |
| <b>Packaging Type</b>    | Bag                               |

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

