


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © 2016 Commscope, INC. Confidential NOTICE: These drawings and specifications are the proprietary property of COMMSCOPE, INC. and may be used only for the specific purpose authorized in writing by COMMSCOPE, INC.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B		ECR-13-016123	27NOV2013	TvdM	MO
C		ECN 8000018219 REBRANDING	21012017	RCR	SC

1 TRUNK LENGTH "L"
 CABLE LENGTH FROM
 2 METER UP TO 99 METER

PART NUMBER	SEE CUSTOMER DRAWING
X-2055713-Y	2055705



NOTES:

- 1 TOLERANCE LENGTH "L" ACC. TO CUSTOMER DRAWING 2055705
- 2 MARKING ON CONNECTOR HOUSING INDICATES FIBER 1 SIDE
- 3 FIBER PATH A-A / B-B STRAIGHT (FOR ALL MPO CONNECTORS).
- 4 ATTENUATION ≤ 0,75 dB MEASURED AT 1310 AND 1550 nm ACC. IEC 61300-3-4 METHOD B WITH MODAL CONDITION ACC. IS 14763-3, OFSTP-14, IEC 61280-4-1 + CABLE LOSS FOR LENGTHS > 10 METER ACC. TO CUSTOMER DRAWING 2055703
- 5 RETURN LOSS ≥ 35 dB MEASURED IN MATED CONDITION AGAINST REF. CONNECTOR AT 1310 AND 1550 nm.
- 6 TEST RESULT SHEET WITH EACH INDIVIDUALLY PACKED ASSEMBLY
- 7 INFORMATION ON LABEL:
 BARCODE
 PART NUMBER & FACTORY ORDER NUMBER
 CABLE LENGTH ("L")
 UNIQUE SERIAL NUMBER
- 8 PACKAGING:
 - ASSEMBLIES FROM 2 METER UP TO 50 METER WILL BE PACKED IN A CARTON BOX.
 - ASSEMBLIES > 50 METER WILL BE DELIVERED ON A REEL.
- 9 CABLE INFORMATION:
 -CORE DIAMETER: 9/125 μm.
 -OUTER CABLE DIAMETER: 8.0 mm.
 -OUTER CABLE COLOR: YELLOW.
 -OUTER CABLE MATERIAL: LSZH (LOW SMOKE ZERO HALOGEN).
 -CABLE LOSS 0.5 AND 0.4 dB/ km AT 1310 AND 1550 nm.
- 10 ASSEMBLIES FROM 100 METER UP TO 500 METER ACC. TO CUSTOMER DRAWING 2055714.
- 11 CONNECTORS AND TAIL PROTECTION BY A SOFT PLASTIC SLEEVE (PULL ON THIS SLEEVE IS NOT ALLOWED).
- 12 INFORMATION ABOUT A PULL AND PROTECTION KIT ASK YOUR LOCAL SALES REPRESENTATIVE.

FIBER PATH STRAIGHT A-A / B-B		
MPO		MPO
1	→	1
2	→	2
3	→	3
4	→	4
5	→	5
6	→	6
7	→	7
8	→	8
9	→	9
10	→	10
11	→	11
12	→	12

Qty	Description	Item
2	DAT-35 LABEL	5
2	FOAC FAN-OUT	4
4	MPO CONNECTORS	3
L1/ L2	FURCATION TUBE ROUND, YELLOW	2
AR	FOCAB 24 F SM 9/125 YELLOW LSZH	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.vd MEULEN 28JUL2010	COMMSCOPE, INC.	
DIMENSIONS: mm		CHK M.OPPERS 28JUL2010		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T.vd MEULEN 28JUL2010	NAME FOTRK 24 FOLD SM LEAD MPO - MPO FEM STRAIGHT	
0 PLC ± -		PRODUCT SPEC	SIZE A2	
1 PLC ± -		APPLICATION SPEC	DRAWING NO C=2055713	
2 PLC ± -		WEIGHT	RESTRICTED TO	
3 PLC ± -		FINISH	SCALE NTS	
4 PLC ± -			SHEET 1 of 1	
ANGLES ± -			REV C	
MATERIAL			CUSTOMER DRAWING	

2055713