



Blank Coaxial Adapter, ivory

Product Classification

Portfolio	CommScope®
Product Type	Multimedia blank
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

General Specifications

Color	Ivory
Mount Type	Snap-in
Package Quantity	1

Mechanical Specifications

Material Type	High-impact, flame retardant, thermoplastic
----------------------	---

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	5%–95%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

