



SYSTIMAX 360™ iPatch® G2 Multimode OM4 High Density Module, 3 pack

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Portfolio</b>             | SYSTIMAX®   |
| <b>Brand</b>                 | iPatch®   SYSTIMAX 360™   |
| <b>Product Type</b>          | Fiber module  |
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |

## Construction Materials

|                      |  |
|----------------------|--|
| <b>Fiber Type</b>    | OM4, LazrSPEED® 550  |
| <b>Material Type</b> | Acrylonitrile butadiene styrene (ABS)   Polycarbonate (PC) |

## Dimensions

|               |                     |
|---------------|---------------------|
| <b>Depth</b>  | 215.90 mm   8.50 in |
| <b>Height</b> | 82.55 mm   3.25 in  |
| <b>Width</b>  | 152.40 mm   6.00 in |
| <b>Weight</b> | 1.13 kg   2.50 lb   |

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Flammability Rating</b>   | UL 94 V-0                            |
| <b>Operating Temperature</b> | -5 °C to +50 °C (+23 °F to +122 °F)  |
| <b>Relative Humidity</b>     | Up to 95%, non-condensing            |
| <b>Safety Standard</b>       | ACMA   CE   cUL   UL                 |
| <b>Storage Temperature</b>   | -40 °C to +70 °C (-40 °F to +158 °F) |

## General Specifications

|                                     |                 |
|-------------------------------------|-----------------|
| <b>Interface, front</b>             | LC              |
| <b>Total Ports, quantity, front</b> | 144             |
| <b>Interface Feature, front</b>     | Standard        |
| <b>Color, front</b>                 | Aqua            |
| <b>Color, housing</b>               | Black           |
| <b>Intelligence Type</b>            | iPatch® enabled |
| <b>Interface, rear</b>              | MPO             |

|                                 |                   |
|---------------------------------|-------------------|
| <b>Adapters, quantity, rear</b> | 12                |
| <b>Interface Feature, rear</b>  | Reduced footprint |
| <b>Color, rear</b>              | Black             |
| <b>Package Quantity</b>         | 3                 |

## Optical Performance

**Insertion Loss, maximum** 0.47 dB

## Regulatory Compliance/Certifications

| <b>Agency</b>   | <b>Classification</b>  |
|-----------------|--|
| RoHS 2011/65/EU | Compliant  |
| ISO 9001:2015   | Designed, manufactured and/or distributed under this quality management system |

