



SYSTIMAX 360™ iPatch® Panel Manager

OBSOLETE

This product was discontinued on: December 31, 2012

Replaced By

760161380
360-imV-CNTRLR SYSTIMAX 360™ imVision® Controller

760230102
360-imV-CNTRLR-AR SYSTIMAX 360™ imVision® Controller

Product Classification

Portfolio	SYSTIMAX®
Brand	iPatch® SYSTIMAX 360™
Product Type	Controller chassis
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

General Specifications

Color	Black Cool gray
Includes	16 in panel bus jumper 7 ft patch cord Forty-four position bus panel Power supply, 1.25A @ 12 Vdc output, 100-240 Vac 50-60 Hz input
Package Quantity	1

Dimensions

Depth	114.30 mm 4.50 in
Height	44.45 mm 1.75 in
Width	457.20 mm 18.00 in
Weight	1.02 kg 2.25 lb

Mechanical Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate Steel
----------------------	---

Environmental Specifications

Flammability Rating	UL 94 V-0
----------------------------	-----------

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 75%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Safety Standard	ACMA CE cUL UL

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

