



iPatch® M4200i 24 Port UTP Intelligent Universal Modular Panel without Modules

Product Classification

Portfolio	SYSTIMAX®
Brand	imVision® iPatch®
Product Type	RJ45 patch panel
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Depth	25.40 mm 1.00 in
Height	44.45 mm 1.75 in
Weight	0.68 kg 1.50 lb
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	6 6A
--------------------------	--------

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	ACMA CE cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	iPatch® enabled
Total Ports, quantity	24
Cable Type	Unshielded
Color	Black
Includes	Cable management bar Four #12-24 dog point mounting screws Information outlet removal tool Instruction sheet Panel Two #12 washers Two #12-24 screws
Package Quantity	1
Rack Units	1.0

Mechanical Specifications

Panel Style	Straight
Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system

