



SYSTIMAX 360™ GigaSPEED X10D® Evolve High Density Shielded Angled Modular Panel, 24 port

Product Classification

| | |
|------------------------------|---|
| Portfolio | SYSTIMAX® |
| Brand | GigaSPEED X10D® SYSTIMAX 360™ |
| Product Type | RJ45 patch panel |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Dimensions

| | |
|-------------------------------------|----------------------|
| Depth, with cable management | 266.70 mm 10.50 in |
| Height | 44.45 mm 1.75 in |
| Weight | 0.84 kg 1.85 lb |
| Width | 482.60 mm 19.00 in |

Electrical Specifications

| | |
|--|-------------------|
| ANSI/TIA Category | 6A |
| Dielectric Withstand Voltage, RMS, contact-to-contact | 1,000 Vac @ 60 Hz |
| Insulation Resistance, minimum | 500 MOhm |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Relative Humidity | Up to 95%, non-condensing |
| Safety Standard | cUL UL |
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |

General Specifications

| | |
|------------------------------|--------------------------|
| Intelligence Type | iPatch® ready |
| Total Ports, quantity | 24 |
| Cable Type | Shielded |
| Color | Cool gray Satin chrome |
| Package Quantity | 1 |
| Rack Type | EIA 19 in |
| Rack Units | 1.0 |

Mechanical Specifications

| | |
|---------------------------------------|---|
| Panel Style | Angled |
| Conductor Gauge, solid | 22 AWG 24 AWG |
| Conductor Gauge, stranded | 22 AWG 24 AWG |
| Conductor Type | Solid Stranded |
| Contact Plating Material | Precious metals |
| Material Type | High-impact, flame retardant, thermoplastic Powder-coated steel |
| Plug Insertion Life, minimum | 750 times |
| Plug Insertion Life, test plug | IEC 60603-7 compliant plug |
| Plug Retention Force, minimum | 30 lbf 133 N |
| Termination Contact Plating | Nickel |
| Termination Type | IDC |
| Wiring | T568A T568B |

Regulatory Compliance/Certifications

| Agency | Classification |
|-----------------|--|
| RoHS 2011/65/EU | Compliant |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

