



InstaPATCH® Cu GigaSPEED X10D® U/UTP Plenum Preterminated Copper Cable, single row standard density outlet to unterminated, 8 links

Product Classification

| | |
|------------------------------|---------------------------------------------------------------------|
| Portfolio | SYSTIMAX® |
| Brand | GigaSPEED X10D® InstaPATCH® Cu |
| Product Type | Copper trunk cable assembly |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Dimensions

| | |
|-----------------------------|---------------|
| Cord Length, minimum | 5 m 17 ft |
| Cord Length, maximum | 90 m 295 ft |

Electrical Specifications

| | |
|-------------------------------|----------|
| ANSI/TIA Category | 6A |
| dc Resistance, maximum | 0.30 ohm |
| Safety Voltage Rating | 300 V |

Environmental Specifications

| | |
|------------------------------|--------------------------------------|
| Environmental Space | Plenum |
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |

General Specifications

| | |
|---------------------------------------|-------------------------------|
| Cable Type | U/UTP (unshielded) |
| Interface, connector A | Information outlet |
| Interface, connector B | Unterminated |
| Interface Feature, connector A | Single row Standard density |

Mechanical Specifications

| | |
|-----------------------|-------|
| Link Count | 8 |
| Conductor Type | Solid |

Wiring

T568B

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system



Included Products

2091B 4/23 (Product Component—not orderable) — GigaSPEED X10D® 2091B ETL Verified Category 6A U/UTP Cable, 4 pair count

MG5600 (Product Component—not orderable) — GigaSPEED X10D® MG5600 Series Information Outlet