

## imVision® Power Supply 12VDC 3050 mm Power Cord



### Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	imVision®
<b>Product Type</b>	Network controller accessory
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

### General Specifications

<b>Package Quantity</b>	1
-------------------------	---

### Electrical Specifications

**Output Current at Voltage, continuous** 2.08 A @ 12 Vdc

### Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	0 °C to +50 °C (+32 °F to +122 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Safety Standard</b>	C-tick   CE   cUL   GOST   KC

### Regulatory Compliance/Certifications

<b>Agency</b>	RoHS 2011/65/EU	<b>Classification</b>	Compliant
---------------	-----------------	-----------------------	-----------

