

imVision® imPower™



## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	imPower™   imVision®
<b>Product Type</b>	Network controller accessory
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## General Specifications

<b>Color</b>	Black
<b>Package Quantity</b>	1

## Dimensions

<b>Depth</b>	127.00 mm   5.00 in
<b>Height</b>	43.18 mm   1.70 in
<b>Width</b>	76.20 mm   3.00 in
<b>Weight</b>	0.05 kg   0.10 lb

## Mechanical Specifications

<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate
----------------------	---

## Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	0 °C to +50 °C (+32 °F to +122 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Safety Standard</b>	C-tick   CE   cUL   GOST   KC

## Regulatory Compliance/Certifications

<b>Agency</b>	RoHS 2011/65/EU
---------------	-----------------

<b>Classification</b>	Compliant
-----------------------	-----------

