



Straight 12inch diameter, Integrated 4G/5G capable, Concealment Pole, to house and conceal four low-power radios and any other wireless infrastructure equipment inside pole modules.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Includes everything needed for a low-power 4G/5G outdoor small cell site
- Up to 4 low power radios, integrated AC load center/OVP and Disconnect , PoleTop concealment module for LAA/DBRS radio mounting

Product Classification

Product Type Metro cell site enclosure

Dimensions

Depth 323.9 mm | 12.8 in
Depth Note Round
Height Note 5.5 ft tall Radio Concealment Module | 8 ft tall Power Module Base
Pole Diameter 323.9 mm | 12.8 in
Pole Height Options 20.0 ft | 25.0 ft | 30.0 ft | 35.0 ft | 40.0 ft

General Specifications

Color Light Grey (RAL 7035)
Color Notes 760242715AB1HH - Light Grey | 760242715AB2HH - Green | 760242715AB3HH - Black | 760242715AB4HH - Brown | 760242715AB5HH - Beige-Grey | 760242715AB9HH - Metallic Silver | 760242715ABCCH - Faux Concrete | 760242715ABWHH - Pure White
Color Options Beige-Grey (RAL 7006) | Black | Brown (RAL 8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Pure White
Finish Aluminum Chromate
Finish Concealment Covers Powder coated
Material Steel

Electrical Specifications

Power/Fiber Input AC load center with OVP and disconnect

Radio Specifications

Radio Compatibility, Ericsson (3) 2205/2208 (Pole Top) | (4) 2203 (radio concealment module) | 5G Expansion module included | 760242715E
Radio Compatibility, Nokia (2) Airscale Micro Radios - LAA & CBRS (Pole Top) | (2) Airscale micro radios – (radio concealment module) | 5G Expansion module included | 760242715N
Radios Included None

Environmental Specifications

Cooling	Passive Cooling
Thermal Compliance	GR-487

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant



* Footnotes

Pole Height Options Overall AGL Standard Height