



RJ45 Coupler Assembly, category 3, 8-position, right-angle, black

Product Classification

| | |
|------------------------------|--------------------------------------|
| Portfolio | NETCONNECT® |
| Product Type | Modular jack coupler |
| Regional Availability | Asia Latin America North America |

Dimensions

| | |
|---------------|--------------------|
| Depth | 30.73 mm 1.21 in |
| Height | 19.05 mm 0.75 in |
| Width | 14.48 mm 0.57 in |

Electrical Specifications

| | |
|------------------------------|--|
| ANSI/TIA Category | 3 |
| Transmission Standard | ANSI/TIA-568-C.2 ISO/IEC 11801 Class C |

Environmental Specifications

| | |
|----------------------------|-----------|
| Flammability Rating | UL 94 V-0 |
|----------------------------|-----------|

General Specifications

| | |
|-------------------------------------|-----------------------------------|
| Cable Type | Unshielded |
| Color | Black |
| Package Quantity | 1 |
| Panel Cutout, recommended | 14.86 x 19.30 mm (0.59 x 0.76 in) |
| Panel Thickness, recommended | 1.60 mm |

Mechanical Specifications

| | |
|----------------------------------|------------------|
| Conductor Type | Solid Stranded |
| Contact Base Material | Phosphor bronze |
| Contact Plating Material | Gold |
| Contact Plating Thickness | 1.27 µm |

| | |
|-------------------------|---------------|
| Material Type | Polycarbonate |
| Outlet Type | Right angle |
| Termination Type | IDC |
| Wiring | T568A T568B |

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

