

## EHR Series Modular Jack, 8-position, RJ45, category 5e, blue



## Product Classification

<b>Portfolio</b>	NETCONNECT®
<b>Product Series</b>	EHR Series
<b>Product Type</b>	Modular jack
<b>Regional Availability</b>	Asia   Australia/New Zealand

## Dimensions

**Compatible Insulated Conductor Diameter, maximum** 1.450 mm | 0.057 in

## Electrical Specifications

**Transmission Standard** ANSI/TIA-568-C.2 | ISO/IEC 11801 Class D

## Environmental Specifications

**Flammability Rating** UL 94 V-0

## General Specifications

<b>Cable Type</b>	Unshielded
<b>Color</b>	Blue
<b>Includes</b>	Shutter   Strain relief cap
<b>Mount Type</b>	EHR Series faceplates and panels
<b>Package Quantity</b>	1
<b>Packaging Type</b>	Bag
<b>Panel Thickness, recommended</b>	1.60 mm

## Mechanical Specifications

<b>Conductor Gauge, solid</b>	24–22 AWG
<b>Conductor Gauge, stranded</b>	26–24 AWG
<b>Conductor Type</b>	Solid   Stranded
<b>Contact Base Material</b>	Beryllium copper

<b>Contact Plating Material</b>	Gold
<b>Contact Plating Thickness</b>	1.27 µm
<b>Material Type</b>	Polycarbonate
<b>Outlet Type</b>	Standard
<b>Termination Tool</b>	110 Punchdown tool
<b>Termination Type</b>	IDC
<b>Wiring</b>	T568A   T568B

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant

