

SSC-760233122 | 18 in Pole Top



Top of Pole 18in Dia Concealment Enclosure for up to six Ericsson metro cell radios

- Enclosure for holding up to 6 Ericsson metro cell radios directly below a multiband canister antenna
- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures
- Matching light pole or monopole options available

Product Classification

Product Type Metro cell site enclosure

Dimensions

Depth 457.2 mm | 18.0 in
Height 889.0 mm | 35.0 in
Mounting Bolt Circle Diameter 9.50 in | 5.62 in
Weight (unloaded) 34.0 kg | 75.0 lb
Width 457.2 mm | 18.0 in

General Specifications

Color Light Grey (RAL 7035)
Color Notes SSC-760233122E1x1 - Light Grey | SSC-760233122E1x2 - Green | SSC-760233122E1x3 - Black | SSC-760233122E1x4 - Brown
Color Options Black | Brown (RAL 8014) | Green (RAL 6005)
Finish Aluminum Chromate
Finish Concealment Covers Powder coated
Material Aluminum | Steel

Antenna Specifications

Antenna Compatibility, CommScope SSC-760233122E11x 12in dia antenna (NH, NNVVSSP, V4SSPP) | SSC-760233122E15x 8in dia antenna (V360, VVSSP)
Antenna Compatibility, Other Vendors SSC-760233122E12x 16in dia antenna - Kathrein | SSC-760233122E13x 14-15in dia antenna: Amphenol, ACE, Galtronics | SSC-760233122E14x 10in dia Series - Galtronics
Antennas Included None

Radio Specifications

Radio Compatibility, Ericsson (6) 2203 5w radios
Radios Included None

Mechanical Specifications

Mounting Options

Wood poles | Tapered poles | Non-tapered poles

Environmental Specifications

Cooling

Passive Cooling

Thermal Compliance

GR-487

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

