

# PFP-SPS-1600M



Slimline SPS DC Rectifier Module, 1600 Watts

## Product Classification

<b>Product Type</b>	Power supply module
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Dimensions

<b>Depth</b>	205.99 mm   8.11 in
<b>Height</b>	41.66 mm   1.64 in
<b>Weight</b>	1.40 kg   3.08 lb
<b>Width</b>	126.49 mm   4.98 in

## Electrical Specifications

<b>Electrical Safety Standard</b>	CE   CSA C22.2 No. 60950-1-03   UL
<b>Electromagnetic Compatibility/Interference (EMC/EMI)</b>	FCC-CFR, Part 15, sub-part B   GR1089 Class A
<b>Input Current Range</b>	15-12A @ 90-120Vac   7.5A @ 230Vac
<b>Output Voltage Range</b>	-42 to 58 Vdc
<b>Power Efficiency</b>	95 %

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
<b>Standards Compliance</b>	EN 61000-4-2 level 4   GR 1089, Issue 4   GR-63

## General Specifications

<b>Package Quantity</b>	1
<b>Packaging Type</b>	Carton

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Designed, manufactured and/or distributed under this quality management system
ISO 9001:2015	

