



Undercarpet Copper Cable, category 5e, 4-pair, 8 conductors, unshielded, 250 ft, gray

- Exceeds TIA/EIA and ISO specifications for Categories specified
- Exceeds all requirements for Gigabit Ethernet
- Leadfree jacketing

Product Classification

| | |
|------------------------------|--------------------|
| Portfolio | NETCONNECT® |
| Product Series | Undercarpet |
| Product Type | Twisted pair cable |
| Regional Availability | North America |

Construction Materials

| | |
|---------------------------|-------------|
| Conductor Material | Bare copper |
|---------------------------|-------------|

Dimensions

| | |
|---------------------|---------------|
| Cable Length | 76 m 250 ft |
|---------------------|---------------|

Electrical Specifications

| | |
|-----------------------------------|---------|
| ANSI/TIA Category | 5e |
| Operating Voltage, maximum | 80 V |
| Safety Voltage Rating | 300 Vac |

Environmental Specifications

| | |
|------------------------|----|
| Safety Standard | UL |
|------------------------|----|

General Specifications

| | |
|---------------------------------|----------------------------|
| Cable Type | U/UTP (unshielded) |
| Pairs, quantity | 4 |
| Supported Application | Commercial Office Retail |
| Jacket Color | Gray |
| Conductor Gauge, singles | 24 AWG |

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

