

## imVision Controller X



## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	imVision®   iPatch®
<b>Product Type</b>	Controller unit
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## General Specifications

<b>Color</b>	Cool gray
<b>Includes</b>	16 in panel bus jumper   7 ft patch cord   Forty-four position bus panel   Power supply, 2.08A @ 12 Vdc output, 100-240 Vac 50-60 Hz input
<b>Package Quantity</b>	1

## Dimensions

<b>Height</b>	81.28 mm   3.20 in
<b>Width</b>	19.00 mm   0.75 in
<b>Weight</b>	1.29 kg   2.84 lb

## Mechanical Specifications

<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate   Steel
----------------------	---

## Electrical Specifications

<b>Input Voltage</b>	100–240 Vac
<b>Output Current at Voltage, continuous</b>	2.08 A @ 12 Vdc
<b>Power Frequency</b>	50–60 Hz

## Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	0 °C to +50 °C (+32 °F to +122 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Safety Standard</b>	CE   RCM   UL

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU  
ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

