

imVision Controller X (Argentina Only)



Product Classification

Portfolio	SYSTIMAX®
Brand	imVision® iPatch®
Product Type	Controller unit
Regional Availability	Latin America

General Specifications

Color	Cool gray
Includes	16 in panel bus jumper 7 ft patch cord Forty-four position bus panel
Package Quantity	1

Dimensions

Height	81.28 mm 3.20 in
Width	19.00 mm 0.75 in
Weight	1.29 kg 2.84 lb

Mechanical Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate Steel
----------------------	---

Electrical Specifications

Input Voltage	100–240 Vac
Output Current at Voltage, continuous	2.08 A @ 12 Vdc
Power Frequency	50–60 Hz

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	0 °C to +50 °C (+32 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Safety Standard	CE RCM UL

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

