



SYSTIMAX 360™ imVision® Controller

OBSOLETE

This product was discontinued on: January 31, 2019

Replaced By

760237877

imV-CNTRL-X-AR

imVision Controller X (Argentina Only)

Product Classification

Portfolio	SYSTIMAX®
Brand	imVision® iPatch®
Product Type	Controller unit
Regional Availability	Latin America

General Specifications

Color	Cool gray
Includes	16 in panel bus jumper 7 ft patch cord Forty-four position bus panel Power supply, 1.25A @ 12 Vdc output, 100-240 Vac 50-60 Hz input
Package Quantity	1

Dimensions

Depth	211.33 mm 8.32 in
Height	81.28 mm 3.20 in
Width	19.00 mm 0.75 in
Weight	1.29 kg 2.84 lb

Mechanical Specifications

Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate Steel
----------------------	---

Electrical Specifications

Input Voltage	100–240 Vac
Output Current at Voltage, continuous	1.25 A @ 12 Vdc
Power Frequency	50–60 Hz

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	0 °C to +50 °C (+32 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Safety Standard	C-tick CE cUL GOST KC

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

