



SYSTIMAX 360™ iPatch® G2 LC Fiber Panel, fixed

Product Classification

Portfolio	SYSTIMAX®
Brand	iPatch® LazrSPEED® SYSTIMAX 360™
Product Type	Fiber patch panel
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Construction Materials

Fiber Mode	Multimode Singlemode
Material Type	Acrylonitrile butadiene styrene (ABS) Polycarbonate (PC)

Dimensions

Depth	323.85 mm 12.75 in
Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in
Weight	1.81 kg 4.00 lb

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	ACMA CE cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	iPatch® enabled
Rack Units	1.0
Shelf Movement	Fixed
Body Style	Duplex
Color	Black
Interface, front	LC
Package Quantity	1
Total Ports, quantity	24

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

RoHS 2011/65/EU
ISO 9001:2015

Compliant
Designed, manufactured and/or distributed under this quality management system

