

## HD iPATCH 2U 64-MPO Distribution Panel, Sliding Panel



### Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	imVision®   iPatch®
<b>Product Series</b>	HD
<b>Product Type</b>	Fiber patch panel
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

### Construction Materials

<b>Material Type</b>	Steel
----------------------	-------

### Dimensions

<b>Depth</b>	539.75 mm   21.25 in
<b>Height</b>	88.90 mm   3.50 in
<b>Width</b>	482.60 mm   19.00 in
<b>Material Thickness</b>	19.0 ga   0.9 mm

### General Specifications

<b>Intelligence Type</b>	iPatch® enabled
<b>Rack Units</b>	2.0
<b>Shelf Movement</b>	Sliding
<b>Color</b>	Black
<b>Interface, front</b>	LC
<b>Package Quantity</b>	1
<b>Total Ports, quantity</b>	64

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

